

| CIRCULAR MAGNETRONS | 2" Target | 3" Target | 4" Target |
|---|------------------------|--------------------|------------------|
| Max. Power (direct cooling) | | | |
| DC, DC Pulsed, HiPIMS: | 400 W | 800 W | 1600 W |
| RF; | 200 W | 400 W | 750 W |
| Max Power (indirect coling) | | | |
| DC, DC Pulsed, HiPIMS: | 250 W | 500 W | 1000 W |
| RF; | 100 W | 200 W | 400 W |
| RECTANGULAR MAGNETRONS | | Max Density | |
| Direct Cooling | | | |
| DC, DC Pulsed, HiPIMS: | 15 W / cm ² | | |
| RF; | 10 W / cm ² | | |
| Indirect Cooling | | | |
| DC, DC Pulsed, HiPIMS: | 8 W / cm ² | | |
| RF; | 4 W / cm ² | | |
| POWER SUPPLIES | | Properties | |
| DC (AIR COOLED) | | 500 W (1000 V -1A) | |
| | | 200 W | |
| RF (air cooled) and Matching Network (automatic) | | 300 W | |
| | | 400 W | |
| | | 750 W | |
| Arc Generator | | 150 A | |
| (for CAE sources air cooled) | | 250 A | |